

## Technical data sheet

Article number:  
924-00372

**RD2-10**

|                                         |                                      |
|-----------------------------------------|--------------------------------------|
| Product Group                           | Ring Terminals                       |
| Product Family                          | Double Grip Pre-Insulated            |
| Material                                | Copper (CU), Polyvinylchloride (PVC) |
| Colour                                  | Blue (BU)                            |
|                                         |                                      |
| Application Range                       | Low Voltage                          |
| Application Tool                        | HYYT7                                |
| Conductor Size Range mm <sup>2</sup>    | 1.5-2.5 mm <sup>2</sup>              |
| Diameter (D)                            | 5.3 mm                               |
| for Hole Ø (FH)                         | 10.5 mm                              |
| Length (L)                              | 31.4 mm                              |
| Length (L2)                             | 10.7 mm                              |
| Length (L3)                             | 20.7 mm                              |
| Max Current                             | 27 A                                 |
| Max Voltage                             | 600 V                                |
| Operating Temperature                   | +75 °C                               |
| Package Content                         | 100 pcs.                             |
| Package Content packed in               | bag                                  |
| REACH Reg. Art.33 does not contain SVHC | Yes                                  |
| ROHS compliant                          | Yes                                  |
| Width (W)                               | 13.7 mm                              |

