

STANLEY

STANLEY Laser Distance Measurer 30M (TLM99)

STHT1-77138



Features:

- 30m working range
- Accuracy of +/- 2mm @10m
- Provides distance, area and volume calculations
- Continuous measurement "tracking" function finds distance from a target quickly and easily
- Measurement taken from either the front or back of the product
- Addition/ Subtraction calculator
- Rated to IP54 to protect against debris
- Runs on 2 x AAA batteries (supplied)

Description:

The STANLEY Laser Distance Measurer TLM99 determines distance, area and volume and has a working range of up to 30m with an accuracy of +/- 2mm @ 10m. The TLM is rated to IP54 to protect against dust and water spray. Compact and lightweight, the TLM99 has a point and click measurement function and runs with 2 x AAA batteries. The TLM99 has a continuous measurement "tracking" function which finds distance from a target quickly and easily along with measurements in out of reach areas. Easily capture measurements, especially those that would be difficult to capture with a tape measure. Equipped with a multitude of convenient features that make any tradesman's life on the job easier, the TLM99 is ideal for electricians, contractors, masons, remodelers, painters, architects, inspectors, and builders.

Specifications

| Product Info | |
|------------------------|-------------------|
| SKU | STHT1-77138 |
| Type | TLM |
| Beam Colour | Red |
| Measuring Range | 0.15-30M |
| Measure Accuracy | +/- 0.2mm/m |
| Distance | Yes |
| Continuous Measurement | Yes |
| Area & Volume | Yes |
| Add & Subtract | Yes |
| IP Rating | IP54 |
| Measuring Points | 2 |
| Memory | Last 4 on screen |
| Batteries (Supplied) | 2 x AAA batteries |
| Kit Contents | TLM99 |