

Endress+Hauser Thermometer TM111-AACAAX1ABC3AA1BA1

Our trend-setting, explosion-proof thermometer is designed for a wide range of industrial applications and hazardous areas



Picture for reference only. Product appearance may vary based on configuration

Configuration of TM111-AACAAX1ABC3AA1BA1:

Approval:	AA	Non-hazardous area
Insert Diameter:	C	6mm
Process Connection; Material:	AA	W/o
Immersion Length U:	X1	395MM..... mm (=<1000mm)
Lagging Length T:	A	0mm, w/o lagging
Sensor Type; Measuring Range; Material:	B	1xPt100 WW; -200...+600oC; 316L
Sensor Standard; Classification:	C	IEC60751; class A, 4-wire
Electrical Connection:	3A	4-20mA HART, 1-channel TMT72, head transmitter DIN B
Terminal Head,Material,Protection Class:	A1	TA30A comfort flip cover; Alu; IP66/68
Cable Entry Terminal Head:	B	1x NPT1/2 female thread
Device Model:	A1	1
Upper range value		150.00°C
Low range value		0.00°C

Alternative part number: TM111-1KAM0/101