



Datasheet

Stock No: 362-6778

Straight Male 2in Part D Cam & Groove Coupler, 2 in BSP, Aluminium



Product Details

Part D Coupler

Cam female x female BSPT
Aluminium coupling with stainless steel pins and brass handles

Cam & Groove Couplings - Aluminium

Conform to MIL-C-27487
Buna-N sealing ring
Working pressure 17 bar (250psi)
Seal temperature range -40°C to +80°C

Specifications:

Hose Inner Diameter	2in
Coupling Connector Type	Part D Cam & Groove Coupler
Body Material	Aluminium
Threaded Connection	2 in BSP
Thread Size	2in
Coupling Gender	Male
Coupling Connector Direction	Straight
Thread Standard	BSP
Maximum Working Pressure	17 bar