



**375**  
LUMEN



**3-6H**  
RUNTIME



**26M**  
RANGE



**IP54/IK07**  
IP RATING


## NEW IL-375R - SLIM RECHARGEABLE POCKET INSPECTION LIGHT

- 375 Lumen white COB LED, 6500k
- Secondary rear 250 lumen white COB LED, 6500k
- Extra top torch - 100 lumen SMD LED, 6500k
- Ultra lightweight compact pocket size
- 180° vertical folding head
- Super tough IK07 copolymer and aluminium construction
- Useful pocket clip
- Strong magnetic base and dual rear magnets
- High quality 1100mAh li-ion battery
- Quick 1A USB Type-C charging - 3 hour charge time
- 1m high quality USB Type-C cable included

**BATTERY** 3.7v 1100mAh Li-ion Rechargeable Battery

**WEIGHT** 80.8g

**DIMENSION** folded 156 x 33 x 20.6 mm / extended 298 x 26 x 20.6 mm



ADDITIONAL TOP TORCH



SECONDARY REAR COB LED