Slide Compound Mitre Saw LXT®

DLS714N

18V X2 • 190 mm • 5 700 min^{-1}

Efficient brushless cordless saw for demanding use

A quick and efficient saw with a dual slide system for cutting large pieces as well as skirting boards. The tool's two 18V LXT batteries and brushless motor achieve a 36V capacity, providing cutting speed that is comparable to electric mitre saws.



Technical specifications

Brushless Motor	✓
Capacity 90°	52 x 300 mm
Nominal Battery Voltage	2 x 18 V
Voltage LXT	✓
No load speed	5700 min^{-1}
Capacity 45°	52 x 212 mm
Capacity 45° left	40 x 300 mm
Max. Bevel Range (Left)	45 / 5 °
Max. Mitre Range (Left)	47 / 57 °
Blade Diameter	190 mm
Bore Size (Arbor Diameter)	20 mm
Sound Power Level (L_{WA})	97 dB(A)
Sound Pressure Level (L_{pA})	88 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level (3 axes)	≤ 2,5 m/s²
Vibration Uncertainty (K Factor)	1,5 m/s²

User benefits

- The double slide mechanism takes up little space and ensures vibration-free precise cutting
- Brushless maintenance-free and long-life motor
- ADT (Automatic torque Drive Technology) adjusts speed and torque during operation for optimum performance
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makitauk.com

Related products

Other

User manual