

AMP

AMP Connect

MAIN MENU

HELP

FAMILIES

REGISTRATION

Alphabetical

Picture

Part Number

SEARCH

SEARCH

SEARCH

Go To Step Search™ Screen

**719554-3** -- 1 of 1 products

Terminals and Splices

AMPOWER II and III/AMPOWER R Terminals and Splices

General **INFO**

Sales **INFO**



Line art represents typical product only.

 [Line Art](#)

<i><b>Searchable Features:</b></i>	
<b>Product Type</b>	Terminal
<b>Product Series</b>	AMPOWER III
<b># of Holes</b>	1
<b>Wire Size</b>	[50.00 <sup>2</sup> ] AWG [mm]
<b>Stud Size</b>	10
<i><b>Other Properties:</b></i>	
<b>Dim. C</b>	.394 [10.00] in. [mm]
<b>Dim. D</b>	.413 [10.50] in. [mm]
<b>Dim. L</b>	1.890 [48.00] in. [mm]
<b>Dim. W</b>	.748 [19.00] in. [mm]
<b>Material</b>	Copper
<b>Plating</b>	Tin
<b>Stud Hole Diameter</b>	.406 [10.30]
<b>Hydraulic Hand Tool</b>	SIMABLOC U 12
<b>Hydraulic Head</b>	HEAD V 13 U NG, HEAD V 20 U NG, Reducer 2S1
<b>Mechanical Hand Tool</b>	ISOLEC III
<b>AMPOWER III Dies</b>	13M+13P AMP III