Features

- For SF24 In-Line Connectors and Panel Mount Connectors
- IP67 (when mated)
- SF24 Series
- Push-Pull Coupling
- Used in Factory Automation, Robotics, Industrial Machinery, Railway & Transportation, Aerospace & Defence, Medical Equipment, Renewable Energy Systems etc.

RS PRO Circular Connector Dust Caps

RS Stock No.: 868160



Image for representational purposes only

RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

The RS Pro SF24 Series offers a range of high-precision, waterproof connectors designed to meet IP67 sealing standards. Featuring a push-pull coupling mechanism, these connectors ensure fast, secure, and reliable mating. The chrome-plated brass housings provide excellent durability while maintaining a sleek, professional appearance.

Available in in-line cable-to-cable and cable-to-panel configurations, the series includes plugs and receptacles with either male pins or female sockets. Suitable for both data and power transmission, the RS Pro SF24 Series is ideal for use in medical, communications, and test & measurement applications.

General Specifications

Shell Material	Brass with chrome plating
Mating Type	Push-Pull
Mating Cycles	500
Colour	Silver

Mechanical Specifications

Connector Series	SF24

Operation Environment Specifications


Operating Temperature	-40^{0}C to 85^{0}C

Protection Category

IP Rating	IP67 (when mated)

Approvals

Compliance/Certifications	RoHS, CE



Mating Parts

In-Line Cable Connectors	Panel-Mount Connectors
868131	868096
868075	868097
868076	868098
868077	868099
868078	868100
868079	868101
868080	868132
868081	868133
868082	868134
868083	868135
868084	868136
868120	868085
868121	868086
868122	868087
868123	868088
868124	868089
868125	868090
868126	868091
868127	868092
868128	868093
868129	868094
868130	868095