Product Datasheet

# RS- 1806823

## Premier Safety Lockout Padlock

### Long Body, PVC Sleeve on Long Steel Shackle - Key Different

### (ES - PLSP 7 - PL - KD - YELLOW)

**Standard features:**

- Each padlock is supplied with 1 key.
- Chrome plated large steel Shackle for better corrosive resistance of 5 mm for best physical strength – duly insulated with PVC black sleeve (making it 6 mm).
- Resistant to extreme temperature changes – $13^0$ F to + $194^0$ F.
- Compact for easy carrying and storage.
- Light weight, solid Aluminium core Safety Padlock
- Made especially for Lockout / Tagout Applications
- Automatic locking for user convenience
- 6 pin brass cylinder
- Insulated body, resistant against heat, dust and debris.
- Compliant with regulations : 1 employee = 1 padlock = 1 key (OSHA).
- Logo printing / Laser engraving optional (front, back, left and right side).
- Key retaining feature (when shackle is open).
- The solid aluminum body is encased by a colored plastic cover for easy identification. To further improve visibility and identification,
- Long Body and shackle insulated against electric shock

**Technical data**

- Comes with 6 mm thick x 62 mm long shackle with sleeve.
- Weight around : 121 grams
- Specified for Lockout / Tagout purpose internationally

**Package includes:**

- Packed single unit in cardboard box.