

Roof plate IP40, W: 850 mm D: 600 mm



Model	
product brand name	SIVACON S4
product designation	top plate
design of the product	IP40 ventilated
design of the surface	zinc plated
design of the product EMC version	No
Protection class	
protection class IP	IP40
Suitability	
suitability for use for outside use	No
Appearance	
color	miscellaneous
Product details	
product component	
• cable entry	No
• ventilation	Yes
Mechanical Design	
height	1.5 mm
width	850 mm
depth	600 mm
net weight	8 kg
material	sheet-steel
Approvals Certificates	
General Product Approval	other



EG-Konf.

[Miscellaneous](#)



[Miscellaneous](#)

other	Environment
Confirmation	Environmental Confirmations
	Environmental Confirmations

Further information
Information on the packaging https://support.industry.siemens.com/cs/ww/en/view/109813875

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8PQ2300-6BA14>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8PQ2300-6BA14>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8PQ2300-6BA14

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

9/1/2023 

