



45° Long Nose Plier - 205 mm

LONG NOSE PLIER

- Precision machined joint for maximum power transmission with optimum leverage for easy and effortless work.
- Integrated ring spanner to tighten or untighten metric bolts (M10).
- Induction hardened cutting edges to cut even the hardest of materials.
- Grey titanium surface finish is non reflective and ensures maximum corrosion resistance.
- Two component handle design for comfortable handling and ergonomic grip.
- Lanyard hole for easy attachment to the Milwaukee safety range to allow use at heights.



Article Number	4932492466
Cutting capacity in hard wire 1800N mm ² [Max. Ø mm]	2.2
Cutting capacity in soft wire 220N mm ² [Max. Ø mm]	3.9
Pack quantity	1