



#### **Datasheet**

# **Cross Connector**

RS Stock number 872-4773



Cross-connection insulated

### **Description:**

The SQI cross-connections for the screw connection system have a pluggable, insulated design. They can be used to conduct the rated current of the corresponding cross-section range. The terminal block design and the variability of the cross-connector ensure excellent flexibility.

## **Specifications:**

Rated current, A   Max. current, A:	57   76
Max. voltage with partition plate, V:	1000
Max. voltage without partition plate, V:	1000
Rated impulse voltage, kV   Contamination degree:	-  3
Pitch, mm:	10

RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.





#### Series overview and accessories:

Terminal blocks colour	RS Article
beige 10mm²	762-2521
blue 10mm²	762-2525

Accessories	RS Article
End plate AP	872-4726
Partition plate TW	501-746
Insulating cap SQIK for cross-connector	872-4739
Insulated cross-connection SQI 2 pole	762-2587
Insulated cross-connection SQI 3 pole	872-4773
Insulated cross-connection SQI 5 pole	762-2590
Insulated cross-connection SQI 10 pole	762-2593

Note: Cross connectors can be used overlapping

Fitting DIN Rails	RS Article
35mm Din Rail, slotted, 500mm	467-406
35mm Din Rail, slotted, 1000mm	467-416
35mm Din Rail, slotted, 2000mm	742-4138
35mm Din Rail, not slotted, 500mm	742-4129
35mm Din Rail, not slotted, 1000mm	467-399
35mm Din Rail, not slotted, 2000mm	467-400