

Datasheet

160mm Single Cut HCS Hand Needle File

RS Stock number [817-9224](#)



Specification:

- Material: Press moulded high carbon steel (k-12) for needle file blade.
- Finish: Neutral colour needle file blades, press cut notch of blade.
- Hardness: Heat treated to HRC: 55 ~ 60 (notch portion of blades)

Contents:

5 pc-160 mm hand type needle file with taper end & knurled hand grip of file, sealed vinyl pouch (diameter of file - 3.0 mm, 28 teeth per centimetre & cut - no.1, minimum working depth of notch - 8.0 cm) (net weight - 60 grams & pouch size- 7.0 cm (w) x 16.5 cm (h))

Remarks:

Material, dimension and hardness ranges of files meet the requirement of factory standard.