



Datasheet

32 Piece Multi-Purpose Security Bit Set

RS Stock number [615-9209](#)



Specification:

- Material: Chrome molybdenum vanadium steel (s-2) for bits, P.P injection holders
- Finish: Sandblast finish for screwdriver bit, red colour (pantone - 187c)for holder
- Hardness: Heat treated to HRC: 56 ~ 62 (screwdriver bits)

Contents:

32 pc-25 mm (1" - l) multi-purpose security bit set with four red colour injection holders (black colour symbol and sizes imprinting) sizes: slotted: 3, 4, 4.5, 5, 5.5, 6, 7 and 8 mm, Phillips / Pozi driver: no.0 no.1, no.2 and no.3 (each kind tip), hex bit: 1.5, 2, 2.5, 3, 4, 5, 5.5 and 6mm, tamper proof trox: t-8, t-10 t-15, t-20, t-25, t-27,t-30 and t-40
1pc-1/4"hexagon 60mm(2-1/4")stainless shaft magnetic bit holder.

Remarks:

Torque and gauge tests meet din-5263,din-5264, din-8764 PH & PZ, din-7422 and cam car textron screwdriver bit standard.