



Rear panel IP40, W: 800 mm

Model	
product brand name	SIVACON S4
product designation	Rear panel
design of the surface	zinc plated
design of the product EMC version	No
Protection class	
protection class IP	IP40
Appearance	
RAL color number	sonstige
color	miscellaneous
Product details	
product component	
• cable entry	No
• lock	No
Mechanical Design	
height	2 000 mm
width	800 mm
depth	25 mm
net weight	22 kg
material	sheet-steel
Approvals Certificates	
General Product Approval	other

[Miscellaneous](#)



[Confirmation](#)

Environment	
Environmental Conformations	Environmental Conformations

Further information	
Information on the packaging	
https://support.industry.siemens.com/cs/ww/en/view/109813875	
Information- and Downloadcenter (Catalogs, Brochures,...)	
http://www.siemens.com/lowvoltage/catalogs	

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8PQ2420-8BA02>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8PQ2420-8BA02>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8PQ2420-8BA02

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

4/4/2025 

