



## PRODUCT-DETAILS

**SP16/M20/M****STR SWL NPB FITTING M20 16MM-MET****General Information**

Extended Product Type	SP16/M20/M
Product ID	7TCA296020R0109
EAN	5020963006692
Catalog Description	STR SWL NPB FITTING M20 16MM-MET
Long Description	3/8 Inch Nickel Plated Brass Straight Swivel Fitting with External Thread, Metric Thread Size M20

**Additional Information**

Product Main Type	Adaptaflex Flexible Cable Protection
Application	For Insertion into Threaded Entries or Knockout to Connect Conduit

**Ordering**

EAN	5020963006692
UPC	786210259192

---

**Technical**


---

Number of Batteries	0
Color	Metallic
Material	Brass
Size	3/8 Inch

---



---

**Environmental**


---

WEEE Category	Product Not in WEEE Scope
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

---



---

**Container Information**


---

Package Level 1 Units	10 piece
Package Level 1 EAN	5020963006692
Package Level 1 Height	7.87 in 200 mm
Package Level 1 Depth / Length	1 in 25 mm
Package Level 1 Width	5.9 in 150 mm

---



---

**Certificates and Declarations**


---

Declaration of Conformity - CE	9AKK107492A9618
RoHS Declaration	9AKK107992A8994
REACH Declaration	9AKK107992A8994

---



---

**External Classifications and Standards**


---

ETIM 8	EC001180 - Screw connection for protective metallic hose
ETIM 9	EC001180 - Screw connection for protective metallic hose
UNSPSC	39121311

---



---

**Categories**


---

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

