

MSA Uncoded SFP+ Module - 10GBASE-BX - 10 Gigabit Ethernet Bi-Directional (BiDi) Fiber Single Strand SFP+ (Upstream) - LC 10km

Product ID: SFP-10GB-BX-U-STA-ST



The SFP-10GB-BX-U-STA-ST is a MSA compliant upstream fiber SFP+ transceiver which pairs with StarTech.com's SFP-10GB-BX-D-STA-ST. They are designed, programmed and tested to work with 10GBASE-BX compatible MSA switches and routers. The SFP+ transceiver module supports a maximum distance of up to 10 km (6.2 mi) and delivers dependable 10 GbE connectivity over fiber cabling.

Technical Specifications:

- Wavelength: 1270nmTx/1330nmRx
- Maximum Data Transfer Rate: 10Gbps
- Type: Single Mode Fiber
- Connection Type: LC Connector
- Maximum Transfer Distance: 10 km (6.2 mi)
- Power Consumption: < 1.3W
- DDM: Yes

This SFP+ fiber module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP Cables, providing the convenience and reliability you need to ensure dependable network performance.

Certifications, Reports and Compatibility



Applications

Features

- **MSA UNCODED SFP+ TRANSCEIVER:** 10 Gigabit Ethernet BiDi Fiber Single Strand SFP+ designed, programmed and tested to work with compatible MSA Compliant switches and routers to deliver reliable 10GbE connectivity
- **INCREASE BANDWIDTH ON EXISTING INFRASTRUCTURE:** This 10 Gigabit Ethernet bi-directional WDM SFP+ transceiver module sends and receives over a single strand of fiber optic cable instead of two
- **TECHNICAL SPECS:** 10GBASE-BX 10Gbps 10G Bi-Directional Upstream Single Mode (SMF) LC Connector 1270nmTx/1330nmRx Digital Diagnostic Monitoring (DDM) Distances up to 10km (6.2mi)
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this SFP module is backed for life (lifetime of module, not network switch), including free lifetime 24/5 multi-lingual technical assistance
- **WORKS WITH MSA COMPLIANT SWITCHES:** Also works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules

Hardware

Warranty	Lifetime
Compatible Brand	MSA Compliant
Industry Standards	IEEE 802.3ae 10GBASE-BX

Performance

Maximum Data Transfer Rate	10.00 Gbps
Max Transfer Distance	10 km (6.2 mi)
Type	Single Mode
Wavelength	1270nmTx/1330nmRx
Fiber Operating Mode	Full-Duplex
DDM	Yes
Compatible Networks	10 Gbps

MTBF 646,156,559 hours

Power Consumption (In Watts) < 1.3W

Physical Characteristics

Product Length 0.5 in [1.4 cm]

Product Width 2.3 in [5.8 cm]

Product Height 0.5 in [1.3 cm]

Weight of Product 0.8 oz [24.0 g]

Packaging Information

Package Length 4.4 in [11.3 cm]

Package Width 3.6 in [9.1 cm]

Package Height 1.3 in [3.3 cm]

Shipping (Package) Weight 1.8 oz [50.0 g]

What's in the Box

Included in Package 1 - SFP+ Transceiver

Warranty Information

Warranty Lifetime

****Product appearance and specifications are subject to change without notice.***