

## FEATURES

- **Sintered Bronze Material:** Provides excellent wear resistance and durability.
- **Flanged Design:** Ensures easy installation and secure alignment.
- **Dynamic Load Rating of 14 N/mm<sup>2</sup>:** Suitable for applications with varying loads.
- **Static Load Rating of 50 N/mm<sup>2</sup>:** Capable of handling high static loads.
- **Outside Diameter of 40.06 mm:** Fits standard housings for seamless integration.
- **Width of 30 mm:** Compact design for space-constrained applications.

## RS PRO 32.03 mm Flanged Plain Bearing

RS Stock No: 558-490



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

This RS PRO flanged plain bearing is designed for applications requiring reliable performance under varying loads. Made from sintered bronze, it offers excellent wear resistance and durability, making it ideal for use in industrial machinery. The flanged design ensures easy installation and alignment, providing a secure fit.

## General Specifications

Bore Size	32.03 mm
Dynamic Load Rating	14 N/mm <sup>2</sup>
Product Type	Plain Bearing
Static Load Rating	50 N/mm <sup>2</sup>
Sub Type	Flanged

## Mechanical Specifications

Material	Sintered Bronze
Outside Diameter	40.06 mm
Width	30 mm

## Approvals

Standards/Approvals	ISO 2795, ISO 9001:2008, UKAS 001
---------------------	-----------------------------------

