

3125RS6W



Products Low Voltage Products and Systems Industrial Plugs and Sockets Plugs & Sockets Surface Socket Outlets

General Information

| | |
|-------------------------------|--|
| Extended Product Type: | 3125RS6W |
| Product ID: | 2CMA167252R1000 |
| EAN: | 7392696672528 |
| Catalog Description: | Surface socket-outlet, 6h, 125A, IP67, 3P+E |
| Long Description: | Surface socket-outlet, earthing sleeve position 6h, rated current 125A, IP67 watertight, 3-poles+earth, frequency 50-60 Hz, color code Red |

Additional Information

| | |
|---|-------------------------------|
| Additional Information: | 3P+E |
| Cable Cross-Section: | 16 ... 70 mm ² |
| Color: | Red |
| Country of Origin: | Czech Republic (CZ) |
| Customs Tariff Number: | 85366990 |
| Data Sheet, Technical Information: | 2CMC700014C0008 |
| Declaration: | 2CMC700005D0001 |
| Declaration of Conformity - CE: | 2CMC700005D0001 |
| Degree of Protection: | IP67 / IP69 |
| E-number: | 2416591 |
| EAN: | 7392696672528 |
| ETIM 4: | EC001321 - CEE socket outlet |
| ETIM 5: | EC001321 - CEE socket outlet |
| ETIM 6: | EC001321 - CEE socket outlet |
| Enclosure Material: | Thermoplastic polyester (PBT) |
| Environmental Information: | 2CMC700001D0002 |
| Frequency (f): | 50 Hz |
| Function: | Surface socket outlet |
| Gross Weight: | 1.7 kg |
| Housing Material: | Thermoplastic (PBT) |
| IIT Publishing Status: | Level 0 - Information enabled |
| Instructions and Manuals: | 2CMC700002D0001 |
| Invoice Description: | Ind. P&S#3125RS6W |
| Minimum Order Quantity: | 1 piece |
| Number of Poles: | 4 |
| Object Classification Code: | 2CMT005069 |
| Package Level 1 EAN: | 7392696672528 |
| Package Level 1 Gross Weight: | 1.7 kg |
| Package Level 1 Height: | 378 mm |
| Package Level 1 Length: | 182 mm |
| Package Level 1 Units: | 1 piece |
| Package Level 1 Width: | 154 mm |
| Product Main Type: | TRS |
| Product Name: | Industrial Socket Outlet |
| Product Net Depth: | 282 mm |
| Product Net Height: | 282 mm |
| Product Net Length: | 171 mm |

| | |
|---|--|
| Product Net Weight: | 1.55 kg |
| Product Net Width: | 145 mm |
| Protection Type: | Watertight |
| Rated Current (I_n): | 125 A |
| Rated Voltage (U_r): | 380 ... 415 V |
| RoHS Date: | L23 |
| RoHS Information: | 2CMC700057D0001 |
| RoHS Status: | Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2006-03-01 |
| Selling Unit of Measure: | piece |
| Short Description: | Surface socket-outlet, 6h, 125A, IP67, 3P+E |
| Size: | 290X145X171 |
| Standards: | IEC 60309-1 IEC 60309-2 |
| Suitable For: | Surface Socket Outlets |
| Suitable for Product Class: | Industrial Plugs and Sockets |
| UNSPSC: | 39120000 |
| Clock Position Of Grounding Contact: | 6 hour |

