

MARQUARDT

SERIES 1800 - SINGLE AND DOUBLE-POLE ROCKER SWITCHES

T0 12 (4) A 250 V AC

single-pole 	Normally closed contact (SPNC)			Normally open contact (SPNO)			Switch (SPDT)						
	1801.6325	1801.1302	1801.1303	1801.6222	1801.1202	1801.2202	1803.1121	1803.2102	1803.2402	1803.2503	1803.5102	1803.6121	1803.6152
Voltage lamp in V													
Actuator color / printing	Black	Black	Red	Black	Black	Black	Black	Black	Black	Black	Black	Black	Black
Housing color	Black	Black	Black	Black	Black	Black	Black	Black	Black	Black	Black	Black	Black
12 (4) A 250 V AC 1E4													
10 (4) A 250 V AC 1E4	•			•			•	•	•	•	•	•	
8 (8) A 250 V AC 5E4													
6 (4) A 250 V AC 5E4	•			•			•	•	•	•	•	•	
6 (2) A 250 V AC 1E4													
4 (3) A 250 V AC 6E3													
4 (2) A 250 V AC 1E4		•	•		•	•							
30 mA 12 V 5E4													
30 mA 12 V DC 5E4													•
15 A 250 V AC 1 1/2 HP													
15 A 125 V AC 3/4 HP													
10 A 250 V AC 1/2 HP	•			•			•					•	
10 A 125 V AC 1/3 HP	•			•			•					•	
6 A 250 V AC 1/2 HP								•	•	•	•		
6 A 125 V AC 1/4 HP								•	•	•	•		
6 A 125 - 250 V AC 1/8 HP													
6 A 125 V AC 1/10 HP		•	•		•	•							
4 A 250 V AC 1/10 HP		•	•		•	•							
Connection type	U	U	U	U	U	U	U	U	U	U	J	U	U
Connection description		4.8	4.8		4.8		4.8						
Inrush current in A (capacitive)													
Contact distance in mm	≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3
Contact material	Au	Au	Au	Au	Au	Au	Au	Au	Au	Au	Au	Au	Au
EN 60335 cap. 30 conform *G*													
Miscellaneous									Installation depth 13.2	Installation depth 16.2			
Stock version		•		•	•	•		•	•	•	•	•	•