



ENGLISH

Datasheet

Trailing Socket 6 Schuko +USB 5m switched



RS Stock Number:

Specifications:

Electrical Rating	16A 250V
Dielectric Strength	1000VAC for 1 min between current carrying parts 2500VAC for 1 min between non-current carrying parts
Operating Temperature	-20 ~ +80°C (-4 ~ 176°F)
Degree of Protection	IP20/NEMA 1

31/07/2017

Features:

- **TUV/GS/S/CE Certified**
- **Trailing Socket 6 Schuko +USB 5m switched**
- **1.5meter,H05VV-F,3G1.5MM cable**