





















		5A		
		Faston terminals	Faston terminals with extended insulation	Solder terminals
<p>1NC + 1NO</p> <p style="text-align: center;">gold plated silver plated</p> 	<p>593 566 000 593 566 100</p> 	<p>593 560 000 593 560 100</p> 	<p>593 561 000 593 561 100</p> 	
<p>1NO</p> <p style="text-align: center;">gold plated</p> 	<p>593 566 020</p> 	<p>593 560 020</p> 	<p>593 561 020</p> 	
<p>1NC</p> <p style="text-align: center;">gold plated</p> 	<p>593 566 050</p> 	<p>593 560 050</p> 	<p>593 561 050</p> 	
<p>2NC + 2NO</p> <p style="text-align: center;">gold plated silver plated</p> 	<p>593 567 000 593 567 100</p> 	<p>593 563 000 593 563 100</p> 	<p>593 564 000 593 564 100</p> 	
Dimensions				
				

Special versions upon request