



Part Number : 1301030014
Product Description : Watertite Wet Location
Incandescent Hand Lamp, 100W with Screw
Release Ungrounded Guard
Series Number : 130103
Status : Active
Product Category : Lamps and Lights
Engineering Number : 1203



Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Lamps and Lights

Series	130103
Description	Watertite Wet Location Incandescent Hand Lamp, 100W with Screw Release Ungrounded Guard
NEMA Configuration	N/A
NEMA Rating	NEMA 4X
Product Name	Watertite
Type	Hand Lamps
UPC	78678861290

Agency

CSA	LR85374
-----	---------

Electrical

Lamp Wattage - Maximum	100W
Lumens	1000
On/Off Switch	No
Voltage (Fixture) - Maximum	120V AC

Physical

Bulb Type	Incandescent
Cord Length - Primary	N/A
Cord Length - Secondary	N/A
Depth	120.65mm (4.750")
Duty	Wet Location
Guard Included	Yes
Guard Type	Screw Release
Height	457.20mm (18.000")
Lamp Type	A21
Length	N/A
Material - Globe	Tempered Glass
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Hand Held
Outlet	None
Packaging Type	Carton

This document was generated on Mar 27, 2025