



Sample photo

Order symbol: ALN 162609
Product nbr: 7811290
Description: Enclosure
Remarks: Aluminium

EAN: 6418074016133
El. number:
Finland: 3420052
Electric No. 8212045729
Denmark:
Electric No. Sweden: 2536327

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

Dimensions:				Accessories:	
mm:	263	162	91	ARM 0825	DIN-15 Mounting rail
inch:	10.4	6.4	3.6	ARH 26	DIN-35 Mounting rail
				MR 75005	Selftapping taptite screw M5
Materials:				MRS 28541	Wall fastening lug (2 pcs)
Material:	Aluminium			PH A & AH A/B	Hinge set
Base colour:	RAL 7001				
Cover screws material:	Stainless steel				
Cover colour:	RAL 7001				
Gasket material:	Polyurethane				
Temperatures:				Rating:	
Temperature °C (short term):	-50 ... 140 °C			Ingress Protection (EN 60529): IP66/IP67/IP68	
Temperature °C (continuous):	-50 ... 80 °C			Impact Resistance (EN 62262): IK08	
Temperature °F (short term):	-60 ... 285 °F			NEMA Class: NEMA 1, 4, 4X, 12, 13	
Temperature °F (continuous):	-60 ... 175 °F				
Accessories:				Certificates:	
AM 1626	Mounting plate			SGS Fimko	

