

# INSULATED SPANNER SET FOAM3 17 PIECES



- Open off set at 15° for easier use
- Approved for live working up to 1,000 volts
- Nonslip handle for maximum comfort
- Tools are hold in place using three colour pre-cut high-density EVA foam
- Design to fit exactly in TengTools service cases
- Chrome vanadium steel construction
- Designed and manufactured to DIN3114 IEC60900 standards
- Organised in a foam inlay module size 3 (FOAM3)

Insulated Spanner Set FOAM3 17 Pieces

## General information

**Country of origin:** Taiwan  
**Barcode:** 5020385044968  
**Tariff code Europe:** 8204110000  
**ECCN US:** EAR99  
**ETIM:** EC011815  
**UNSPSC:** 27111706

## Dimensions

**Net weight (g):** 2215  
**Width (mm):** 433  
**Depth (mm):** 267  
**Height (mm):** 47

## Attributes

**Product type:** Spanners & Wrench Sets, Insulated Tool Sets  
**Certificates:** VDE  
**Number of pieces:** 17  
**Handle type:** Bi-material  
**Insulated:** Yes  
**Unit of measurement:** Metric  
**Inlay material:** FOAM  
**Type of set:** FOAM3

## Features



**FOAM  
SERIES**



Technical changes and errors may occur. 01-08-2024 19:59



**DESIGNED IN SWEDEN**

TengTools is a Swedish company present in more than 30 markets worldwide, and offers hand tools in smart storage solutions for demanding professionals within the automotive, maintenance and engineering sectors, as well as motor sport enthusiasts who aspire to use the same tools as top mechanics across the globe.



Sandbergsvägen 3  
441 39 Alingsås, Sweden

# LIST OF CONTENTS



## **TEFSPV17** Insulated Spanner Set FOAM3 17 Pieces

- MPV600507** Insulated Spanner 7 mm
- MPV600508** Insulated Spanner 8 mm
- MPV600509** Insulated Spanner 9 mm
- MPV600510** Insulated Spanner 10 mm
- MPV600511** Insulated Spanner 11 mm
- MPV600512** Insulated Spanner 12 mm
- MPV600513** Insulated Spanner 13 mm
- MPV600514** Insulated Spanner 14 mm
- MPV600515** Insulated Spanner 15 mm
- MPV600516** Insulated Spanner 16 mm
- MPV600517** Insulated Spanner 17 mm
- MPV600518** Insulated Spanner 18 mm
- MPV600519** Insulated Spanner 19 mm
- MPV600520** Insulated Spanner 20 mm
- MPV600521** Insulated Spanner 21 mm
- MPV600522** Insulated Spanner 22 mm
- MPV600524** Insulated Spanner 24 mm