



mecalectro

## Small linear solenoid for standard use – 8.M15.02.73 (Pull)



**Stroke:** 24 mm

**Force at beginning of stroke (FM: 100/25/5%):**  
1/7.5/27 N

**Force at end of stroke (FM: 100/25/5%):**  
15/60/60 N

**Power Consumption (FM: 100/25/5%):**  
15/53.5/237 W

**Total mass:** 570 g

**Degree of protection / Energetic class:** IP 00 / B

**Standard supplies:** 24Vcc

**Possibles supplies:** From 6 to 250Vcc

**Duty Cycle:** Permanent, impulsions (100 / 40 / 25 / 15 / 5 %)

**Standard:** NF C 79300

**Examples of applications:** various automations, positioning, multiple locks