
HHR35AA Cylindrical 2

Cylindrical 2/3AA size (HR 15/29)






Diameter	14.5 + 0 / - 0.7 mm
Height	28.2 + 0 / - 1.0 mm
Approx.Weight	11g


Specifications

Nominal Voltage		Voltage	1.2V	
Discharge capacity *		Average **	390mAh	
		Rated (min.)	350mAh	
Approx.Internal impedance at 1000Hz at charged state.			30m	
Charge		Standard	35mA × 16hrs.	
		Rapid ***	350mA × 1.2hrs.	
Ф	rature Charge	Standard	0 to 45	
ratur		Rapid	0 to 40	
edwe	Discharge		-10 to 65	
Ambient Temperature	Storage	< 1 year	-20 to 35	
		< 6 months	-20 to 45	
		< 1 month	-20 to 55	





** For reference only.

Battery performance and cycle life are strongly affected by how they are used. In order to maximize battery safety, please consult Panasonic when determining charge/discharge specs, warning label contents and design.



Typical discharge characteristics





^{***} Need specially designed control system. Please contact Panasonic for details.