

IVR-L 65/24-2 KIT

Ideal for the metal processing industry: the compact IVR-L 65/24-2 industrial vacuum kit is suitable for vacuuming and separating liquids and solids such as swarf.



Order no. 9.990-904.0

- 360° working radius

Technical data

EAN code		4066529164131
Power supply	Ph / V / Hz	1 / 220 - 240 / 50 - 60
Air flow	l/s / m³/h	144 / 520
Vacuum	mbar / kPa	235 / 23.5
Container capacity	l	65
Container material		Steel
Rated input power	kW	2.4
Vacuuming type		Electric
Connection nominal diameter		DN 50
Accessory nominal diameter		DN 50 / DN 40
Main filter dust class		L
Filter area for main filter	m²	0.25
Weight without accessories	kg	46
Weight (with accessories)	kg	46.5
Weight incl. packaging	kg	46.5
Dimensions (L × W × H)	mm	711 × 523 × 960

Equipment

Main filter	Surface filter
Accessories included in the scope of delivery	yes
Automatic filling level shut-off	■

- Included in the scope of supply.



Reliable overflow protection

- A float effectively prevents overfilling of the collection container.
- Transparent hose for checking the amount of fluid absorbed.
- The hose is also used for easy emptying.



High robustness, flexibility and modularity

- Machine and chassis very robust and equipped with high wall thicknesses.
- Rotatable hose connection with up to 360° rotatable pipe bend.



Comes with a strainer basket

- Enables easy disposal of vacuumed solids.
- Enables vacuumed liquids to be recovered.
- Very quiet drive head ensures that the cooling air is blown out evenly.

ACCESSORIES FOR IVR-L 65/24-2 KIT 9.990-904.0



	Order no.	Description	
NOZZLES			
Standard nozzles			
Standard nozzle silicone DN50	1 9.988-402.0		■
Floor nozzles			
Aluminium floor nozzle 200 mm DN50	2 9.981-426.0	Floor nozzle, DN 50, with 200 mm suction width.	□
Aluminium floor nozzle, el. 370 mm, DN50	3 9.987-612.0	Electroconductive multi-purpose floor nozzle. 370 mm wide, DN 50.	□
Surface nozzles			
Silicone surface nozzle 120 mm DN50	4 9.988-119.0	Electroconductive rubber nozzle, angled, DN 50, suitable for use with foods.	□
Liquid nozzles			
Liquid nozzle 900 mm DN50	5 9.981-427.0	Bypass nozzle, DN 50, overall length: 1000 mm.	□
HOSES			
PU hoses			
Hose PU DN50 3 m	6 9.989-619.0	Oil-resistant, electroconductive PU hose, DN 50. Suitable for abrasive suction media and temperature-resistant up to 80 °C. Length: 3 m.	■
HANDLES			
Handle DN50, curved	7 9.977-678.0	Electroconductive and 45° curved handle made from stainless steel. Inner cone DN 50.	■
OTHER ACCESSORIES			
Baffle plate Ø 410 mm	8 9.984-119.0	Baffle plate made from plastic with 420 mm diameter for containers and tanks.	■
SUCTION TUBES			
Suction tube 850 mm DN 50	9 9.977-531.0	850 mm long extension tube made from steel. Electroconductive and with inner cone DN 50.	□
EMPTYING SUPPORTS			
Strainer baskets			
Filter basket, stainless steel, Ø 400 mm, 20 l	10 9.980-852.0	Filter basket, stainless steel, 20 l, hole diameter 1.5 mm. For the efficient separation of liquids and shavings.	■
Other emptying aids			
Overfill protection dia. 435 mm	11 9.982-118.0	Float insert, stainless steel, for overfill prevention with ball float, central suction.	□
ACCESSORY SETS			
Accessory kit for liquids			
Liquid/solid accessory kit Expert DN50	12 9.990-879.0	Accessory kit DN50 for liquid vacuums: PU hose 3 m (9.989-619.0), handle (9.977-678.0), standard nozzle (9.988-402.0), surface nozzle 120 mm (9.988-119.0).	□
Accessory kit for liquids/chips			
Oil/swarf accessory kit DN50 Expert	13 9.990-881.0	Accessory kit DN50 for liquid and swarf vacuum: ME-PU hose 3 m (9.989-623.0), handle (9.977-678.0), standard nozzle (9.989-673.0), surface nozzle (9.988-119.0).	□
Advanced liquid floor cleaning set DN50	14 9.990-896.0	Advanced liquid floor cleaning set: EVA hose (9.990-926.0), handle (9.990-928.0), 2 × suction tube (9.990-932.0), floor nozzle (9.990-938.0), standard nozzle (9.980-761.0).	□

■ Included in the scope of supply. □ Available accessories.