Bailey lights
for professionals

RoBust LED **Work Lighting**


For Work and Leisure

bailey.nl

bailey.fr




145637	5m	4000K	380lm/m	220-240V	120˚
145374	50m	4000K	380lm/m	220-240V	120˚



147031	25m	4000K	850lm/m	220-240V	120˚
147089	50m	4000K	850lm/m	220-240V	120˚



146763	25m	3000K	400lm/m	220-240V	360˚
146764	25m	6500K	420lm/m	220-240V	360˚



146803	25m	6500K	1200lm/m	220-240V	120˚

RoBust LED Rope **360°**




147171	25m	Green	5W/m	220-240V	360˚
146765	25m	Red	5W/m	220-240V	360˚



146507	20m	4000K	840lm/m	220-240V	240˚



147107	20m	6500K	1300lm/m	220-240V	240˚



147172	25m	Blue	5W/m	220-240V	360˚
147173	25m	Pink	5W/m	220-240V	360˚



146802	10m	6500K	830lm/m	220-240V	120˚


RoBust LED Rope **Plus**




147032	25m	6500K	1000lm/m	220-240V	120˚



147259	25m	Gold	5W/m	220-240V	360˚



146977	10m	6500K	800lm/m	18V	120˚



147029	5m	4000K	450lm/m	AC42V	120˚
147030	15m	4000K	450lm/m	AC42V	120˚

Accessories **360°** series



146928
Mounting hook for LED Rope and cables



147212
Dimmer Kit for LED Ropes RoBust 360° & 145829 + Remote



146768
Mounting Clip for LED Rope 360° 13mm



146917
Empty Reel for LED Ropes




147100
Empty Trolley for LED Ropes



146769
End Cap for LED Rope 360° 13mm

RoBust LED Rope **Original**




145787	25m	Green	5W/m	220-240V	120˚

Accessories



147220
Dimmer Kit for LED Ropes RoBust Plus + Remote



146947
Microwave Motion Sensor for LED Rope Plus



146946
ON/OFF Switch for LED Rope Plus



146948
Emergency Power Supply for LED Rope Plus



146944
Splitter Y 2-way for LED Rope Plus



146945
Splitter Y 3-way for LED Rope Plus



146927
Mounting clip with Magnet for LED Rope




147256
Aluminum Profile 1M for RoBust LED Rope


Bailey lights
for professionals

Bailey Electric & Electronics b.v.
Everdenberg 21, 4902 TT Oosterhout
sales@bailey.nl | +31 (0)162 52 2446
ventes@bailey.fr | +33 (0)9 75 18 42 48

Check out the Work Lighting here:




LED Corn Mobile



146548	60W	4000K	7200lm	IK08	IP64




146771	15W	6500K	1500lm	IP54	Spot 300lm
146772	20W	6500K	1500lm	IP54	Clamp



147136	40W	6500K	4500lm	18V Battery	IP65



146544	100-250W	4000K	30.000lm	IK08	IP65



146770	10W	6500K	1000lm	IP65	5V
147109	10W	6500K	750lm	IP54	5V


RoBust LED Portable



147242	20W	6500K	2000lm	IK08	IP65




146546	Tripod for RoBust LED Corn Balloon 3.8M M10
146547	Bag for RoBust LED Corn Balloon & Tripod



146904	5W	4-5-8000K	120-500lm	IP44	Red light
147110	6W	6500K	550lm	IP54	Headlamp

RoBust LED Hybrid



147219	50W	6500K	5000lm	IK07	IP54

LED Corn Balloon






LED Floodlights Switch



146587	5m cable	Max. 60W	E27	230V	IP44




146799	50-100W	3000-6500K	7000 - 14000lm		IP66
145820	100-150W	3000-6500K	12500 - 21000lm		IP66
145821	200-300W	3000-6500K	25000 - 42000lm		IP66



147111	5W	6500K	550lm	IP67	3XAAA (ex.)

Renovation Lamps




140818	10W	4000K	935lm/m	220-240V	10-pack
146699	11W	4000K	1055lm/m	220-240V	3-pack

LED Floodlights



145388	10W	1400lm
145389	20W	2800lm
145390	30W	4200lm
145391	50W	7000lm



145748	50W	RED
145749	50W	GREEN
145750	50W	BLUE

RoBust LED Charge

