



18V XR Brushless 184mm Rail Compatible Circular Saw

DCS572P2-QW

DEWALT Brushless Motor for extended run-time, reliability & durability
General purpose ripping, cross-cutting and bevelling circular saw for wood
and other construction materials

Variable adjustment of the bevel angle to 57 degrees

Optimum balance for safe, fatigue-free operation

Stable block construction for low vibration running and long service life



Sound Power	102 dB(A)
-------------	-----------

Sound Pressure Uncertainty	3 dB(A)
----------------------------	---------

Sound Pressure	91 dB(A)
----------------	----------

Uncertainty K 1 (Vibration)	1.5 m/s ²
-----------------------------	----------------------

Power Source	Cordless
--------------	----------

No Load Speed	5500 Rpm
---------------	----------