


Technical data

51406

One direction thrust ball bearings

VISUAL (S)



PRODUCT DEFINITION

Brand	NTN
d - Internal diameter	30 mm
D - External diameter	70 mm
T - Thrust bearing height	28 mm
rs - Min fillet radius	1 mm
Mass	0,516 kg

PRODUCT PERFORMANCE

Ca - Dynamic axial load rating	72500000 mN
C0a - Static axial load rating	126000000 mN
Cua - Limit axial load rating	5650000 mN
N lim - Oil lubrication limit speed	19200 °/s
N lim - Grease lubrication limit speed	13200 °/s
Tmin - Min operating temperature	233,15 °K
Tmax - Max operating temperature	393,15 °K

ABUTMENT

Da max - Max shoulder diameter OR	46 mm
da min - Min shoulder diameter IR	54 mm

