



See online  
technical sheet

## / MS41 17

1000V Insulated ratchet ring spanner 6-sided

## / Standards

- Standards : NF EN 60900, IEC 60900



## / Use

The tool enables high-torque tightening to be carried out very quickly in hard-to-reach areas.

## / Advantages

- The thickness of the insulation on the working head has been reduced to ensure excellent accessibility
- Easy to use; can be reversed by turning the tool over

## / Technical specifications

- Clamping key kind : isolate
- Length (mm) : 185
- clamping-key-opening-size : 17
- Sides number : 6 sides
- General acceptance (mm) : 15
- Recovery angle : 5°

