

# CZL50-10CB



CU CIRCUIT BREAKER LUG 50SQMM M10



Product image  
not available

## General Information

Extended Product Type	CZL50-10CB
Product ID	7TBH007940R0267
EAN	5415022377828
Catalog Description	CU CIRCUIT BREAKER LUG 50SQMM M10
Long Description	Copper One-Hole (Circuit Breaker) Metric Lug, Long Barrel - Narrow Tongue, Bell Shaped End, Cable Size 50mm <sup>2</sup> , Stud Size M10, Length 49mm, Flat 21mm, Hole Spacing 9mm

## Ordering

EAN	5415022377828
Minimum Order Quantity	800 piece
Customs Tariff Number	8536904000

## Dimensions

Product Net Weight	22.172 g
--------------------	----------

## Container Information

Package Level 1 Width	199.898 mm
Package Level 1 Height	102.108 mm
Package Level 1 Depth / Length	72.898 mm
Package Level 2 Units	800 piece
Package Level 2 Width	320.04 mm
Package Level 2 Height	220.98 mm
Package Level 2 Depth / Length	215.9 mm
Package Level 3 Units	800 piece

## Additional Information

Brand / Label	Spec-Kon
Insulation Material	None
Material	Copper
Product Main Type	COMPRESSION CONNECTORS
Product Name	COPPER LUG
Product Type	Copper One Hole Narrow Tongue Bell-Shaped End Metric Lug

UPC

786210081823

---

---

### Certificates and Declarations (Document Number)

---

Data Sheet, Technical Information	CZL50-10CB
Instructions and Manuals	CZL50-10CB

---

---

### Classifications

---

ETIM 6	EC001051 - Tube cable lug for copper conductors
UNSPSC	39121405
WEEE Category	Product Not in WEEE Scope

---

---

### Categories

---

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Compression & Mechanical Connectors



Product image  
not available