

CD881 - WX2 Eco Stretch Trade Trousers

Collection: WX2

Range: Workwear

Shell Fabric: Kingsmill Polycotton Eco: 65% Recycled Polyester, 35% Cotton

Outer Carton: 24

Product information

The WX2 trade trouser with stretch is perfect for the trade person or your professional DIYer. This trouser has every thing you need with zip ventilation on the back of the legs and knee pad pockets.

WX2

WX2™ is a new eco-conscious workwear collection. All products are constructed using GRS recycled fabrics and are available in a number colourways allowing wearers to choose a colour to suit their professional environment.

Workwear

Portwest workwear offers a range of designs and features suitable for many end uses. Quality fabrics and construction techniques are used guaranteeing comfort and safety. Tested to withstand the rigours of everyday wear each garment has been carefully designed and manufactured to ensure optimum quality at the best price.



Features

- Hard wearing durable twill fabric with excellent dye retention
- Eco conscious product made using certified recycled or sustainable material
- Innovative stretch panelling in key movement areas provides excellent comfort and flexibility
- 10 pockets for ample storage
- 2 Side pockets
- 2 Back pockets
- 1 Thigh pocket with zip closure
- 1 Rule pocket
- 1 Spanner pocket
- Knee pad pockets to facilitate knee pads
- Easy access cargo pockets

CD881 - WX2 Eco Stretch Trade Trousers

Commodity Code: 6203431100

Test House

Wash Care



Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
CD881DNR28	Dark Navy	60.0	40.0	30.0	0.5920	0.0720	5036108394753	15036108879615
CD881DNR30	Dark Navy	60.0	40.0	30.0	0.6170	0.0720	5036108394760	15036108879622
CD881DNR32	Dark Navy	60.0	40.0	30.0	0.6350	0.0720	5036108394777	15036108879639
CD881DNR33	Dark Navy	60.0	40.0	30.0	0.6460	0.0720	5036108395323	15036108879745
CD881DNR34	Dark Navy	60.0	40.0	30.0	0.6520	0.0720	5036108394784	15036108879646
CD881DNR36	Dark Navy	60.0	40.0	30.0	0.6670	0.0720	5036108394791	15036108879653
CD881DNR38	Dark Navy	60.0	40.0	30.0	0.6860	0.0720	5036108394807	15036108879660
CD881DNR40	Dark Navy	60.0	40.0	30.0	0.7130	0.0720	5036108394814	15036108879677
CD881DNR41	Dark Navy	60.0	40.0	33.0	0.7210	0.0792	5036108395330	15036108879752
CD881DNR42	Dark Navy	60.0	40.0	33.0	0.7430	0.0792	5036108394821	15036108879684
CD881DNR44	Dark Navy	60.0	40.0	33.0	0.7700	0.0792	5036108394838	15036108879691
CD881DNR46	Dark Navy	60.0	40.0	33.0	0.7860	0.0792	5036108394845	15036108879707
CD881DNR48	Dark Navy	60.0	40.0	33.0	0.8080	0.0792	5036108394852	15036108879714