

Spécifications



Eaton CAP320900

Eaton Crouse-Hinds series CAPRIPLAST flexible conduit, Size 9, Grey, 11.5mm I.D., Galvanized steel with PVC coating, 15.6mm O.D., -5°C to +60°C

Spécifications générales

PRODUCT NAME	Eaton's Crouse-Hinds series CAPRIPLAST flexible conduit
CATALOG NUMBER	CAP320900
EAN	3589353209003
PRODUCT LENGTH/DEPTH	50000 mm
PRODUCT HEIGHT	15.2 mm
PRODUCT WIDTH	15.2 mm
PRODUCT WEIGHT	220 g

Spécifications du produit

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	IEC
MATERIAL	Galvanized steel with PVC coating
TEMPERATURE RATING	-5°C to +60°C
TRANSPARENT	No
OUTSIDE WALL COLOR	Grey
SPIRAL MATERIAL	Steel PVC coating
NOMINAL INNER DIAMETER	11.5 mm
INTERNAL DIAMETER	11.5 mm
MEDIUM TEMPERATURE (CONTINUOUS) - MAX	60 °C
MEDIUM TEMPERATURE (CONTINUOUS) - MIN	-5 °C
BENDING RADIUS	32 mm
STATIC WIRE	Yes
FITTED WITH:	Exterior Spiral

Ressources

PEP ECO-PASSPORT	eaton-conduit-and-tubing-pep-eato-00442-v0101-en.pdf
------------------	--

NOM DU PROJET:

NUMÉRO DU PROJET:

PRÉPARÉ PAR:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Irlande
Eaton.com

© 2026 Eaton. Tous droits réservés.

Suivez-nous sur les réseaux sociaux pour connaître les dernières informations concernant nos produits.

