



ノイズに強いシールドタイプ、ツメの折れないコネクタ採用のCAT5eSTP LANケーブル。
ブルー。

KB-STPTS-005BL : 0.5m
KB-STPTS-01BL : 1.0m
KB-STPTS-02BL : 2.0m
KB-STPTS-03BL : 3.0m
KB-STPTS-05BL : 5.0m
KB-STPTS-10BL : 10.0m



仕様

カテゴリ	CAT5e
規格名	1000BASE-T
対応カテゴリ・規格	カテゴリ5e (1000BASE-T)、カテゴリ5 (100BASE-TX)、カテゴリ3 (10BASE-T) 適合
通信速度	1Gbps
周波数特性	100MHz
ケーブル長	0.5~10.0m
カラー	ブルー
ケーブル直径	5.5mm
ケーブル芯数	8芯 (4P)
結線仕様	ストレート結線
ケーブル構造	STP
十字介在	なし
最小曲げ半径	敷設時/55.0mm 敷設後/44.0mm
ケーブル導体	26AWG
ケーブル導体構造	より線
PoE	対応

被覆材質	PVC
色配線	TIA/EIA-568A
コネクタ形状	RJ-45コネクタ
スリムコネクタ	あり
ツメ折れ防止コネクタ	あり
ツメ折れ防止カバー	あり
使用温度範囲	-10～80°C
検査	100%導通検査

特長

曲げても折れないナイロン製ツメと弾力性に優れたPVC（ポリ塩化ビニル）製ツメ折れ防止カバー、丈夫なポリカーボネート製コネクタで、信頼の三重構造です。

伝送速度1000Mbps（1Gbps）のギガビットイーサネットに対応したカテゴリ5e適合のLANケーブルです。

ツイストペアケーブルをさらにシールドでカバーした、ノイズに強いケーブルです。

より線仕様なので、柔らかく取り回ししやすくなっています。

対応情報

対応環境（機器）	ADSLモデム、CATVモデム、FTTH、デジタルテレビ、ハードディスクレコーダー（RJ-45ポートを持つ機種）、INS64（30m以下）対応
製品関連ページ	<ul style="list-style-type: none">・ LANケーブルの選び方はこちら・ 「LAN PROFESSIONAL LANケーブルの加工法と最新情報」はこちら・ ケーブル特注サービスはこちら・ LANケーブル比較表はこちら

CAT5eSTP LAN cable, 0.5 to10.0m, blue, with a noise-resistant shield and unbreakable connectors.

KB-STPTS-005BL : 0.5m

KB-STPTS-01BL : 1.0m

KB-STPTS-02BL : 2.0m

KB-STPTS-03BL : 3.0m

KB-STPTS-05BL : 5.0m

KB-STPTS-10BL : 10.0m

Specification

- Category : CAT5e
- Standard name : 1000BASE-T
- Supported categories and standards : Category 5e (1000BASE-T), Category 5 (100BASE-TX), Category 3 (10BASE-T) compatible
- communication speed : 1Gbps
- Frequency response : 100MHz
- Cable length : 0.5 to 10.0m
- Color : blue
- Cable diameter : 5.5mm
- Number of cable cores : 8-core (4P)
- Wiring specifications : Straight connection
- Cable Structure : STP
- Cross intervention : none
- Minimum bending radius : When laying/55.0mm
After laying/44.0mm
- Cable conductor : 26AWG
- Cable conductor structure : Stranded wire
- PoE : correspondence
- Coating Material : PVC
- Colored wiring : TIA/EIA-568A
- Connector Shape : RJ-45 Connector
- Slim Connector : can be
- Anti-break connector : can be
- Claw breakage prevention cover : can be
- Operating temperature range : -10 to 80° C
- Inspection : 100% continuity test

Features

- It has a reliable triple structure with nylon claws that will not break even when bent, a claw breakage prevention cover made of highly elastic PVC (polyvinyl chloride), and a durable polycarbonate connector.
- This is a Category 5e compliant LAN cable that supports Gigabit Ethernet with a transmission speed of 1000Mbps (1Gbps).
- This cable is resistant to noise as the twisted pair cable is further covered with a shield.
- The wire is stranded, making it flexible and easy to handle.