



Generator
Model: **LC2500DC**



- Durable, Professional Generator
- High performance rating
- Sturdy Roll-over frame
- Dual Voltage system
- Electric start and wheel kits optional
- Low noise level
- Fuel efficient for 13 hrs autonomous running



Generator

Model: **LC2500DC**

SPECIFICATION:

ENGINE	single cylinder, Forced Air cooled, 4 stroke	
	Rated Power (KW/3000rpm)	3.8
	Starting System	Recoil Start
	Ignition system	T.C.I.
	Displacement (cc)	196
	Fuel Consumption (L/ hr)	1.22
	Fuel Tank Capacity	15
	Oil Capacity (L)	0.6
	Noise level	65 (at 7m)
	Continuing operating hours (h)	13
GENERATOR	Charging Voltage V	12 (DC)
	Charging Current A	8.3
	Rated Frequency (HZ)	50/60
	Rated Voltage (V)	110/220/230/240
	Rated Power (KW)	2
	Max. Power (KW)	2.2
DIMENSIONS	L(mm)×W(mm)×H(mm)	590×475×460
	Dry Weight (kg)	45
ACCESSORIES	Large-size air cleaner	○
	Large-size muffler	○
	Large-size fuel tank	○
	Fuel Gauge	○
	Voltmeter	○
	Automatic voltage regulator	○
	Oil alarming system	○
	Non-fuse breaker	○
	Battery holder	—