

Technical sheet

PLE600

Manhole cover 600 mm (24") – Max load 150 kg

Anti-slip temporary manhole cover with a diameter of 600 mm, used to cover sewer openings during maintenance operations to protect workers from accidents on construction sites. Made of low-density linear polyethylene, it supports up to 150 kg and withstands temperatures ranging from -40 to +60°C.







Customs code	3926909790
EAN	3321360107725

Color : Black

Material : LLDPE

Specifications :

- Made from LLPDE and equipped with an anti-slip surface.
- Easy to transport and store.
- Two handles and cable openings.
- Size: 60 cm.

Diameter (mm)	Maximum dynamic load (kg)	Net weight (kg)
600	150	5,90

VISO
www.viso-cpn.com

VISO - 7 avenue Arago - ZI de la Vigne aux Loups - 91380 CHILLY-MAZARIN - France

Tél. + 33 (0)1 69 53 46 70 - Fax + 33 (0)1 69 53 46 80 - contact@viso-cpn.com / commande@viso-cpn.com