

VARTA Recharge Accu Power AAA 1000 mAh Blister 4



The most powerful product line with durable and precise energy supply for all standard and smart applications of daily use.



Information

- Highest 'ready to use' capacity for AAA NiMH batteries with 1000mAh
- Pre-charged and with 'ready to use' technology - for immediate usage straight from the pack
- Rechargeable hundreds of times without memory effect
- Suitable for the most demanding standard and smart devices of daily use and all NiMH chargers
- Best use in high drain applications like game controllers, toys, photoflashes and more
- Lasts up to 10 times longer in digital cameras*
- * vs. VARTA Energy. Based on IEC 60086-2 (ed. 14.0) DSC-Test for FR10G445. May vary by device.

Article Details

Ordernumber	05703 301 404
Customs Tariff Number	85075000
Country Of Origin	China
IEC	HR03
Others	HC1000AAA, AAA, Ministilo
Nominal Capacity	1000 mAh
Voltage	1.20
System	Nickel Hydride
Consumer Unit	4
DG Profile	NiMH battery UN3496 (sea to 100kg ok)

Logistical Data

	Content (SU)	GTIN / EAN	Facing (mm)	Depth (mm)	Height (mm)	Weight (kg)
VBE (Selling unit)	1	40 08496 594375	80.00	12.30	120.00	0.07
SK2 (Inner carton 2)						
SK1 (Inner carton 1)	10	40 08496 594382	69.50	126.00	83.00	0.67
VSK (Master carton)	50	40 08496 594399	135.00	357.00	90.00	3.44
PAL (Pallet)	10800	40 08496 748822	800.00	1,200.00	1,230.00	763.78
Layer / Pallet	Master carton / Layer		Master carton / Pallet		Minimum pieces / shipment unit	
12	18		216		10	

All mentioned products and specifications are subject to change. In case of non-availability of any product or item, VARTA Consumer Batteries GmbH & Co. KGaA cannot be held responsible. Some of the products shown may not be available in all countries. The pictures might be different to the original products. Technical changes and errors reserved.

VARTA Consumer Batteries GmbH & Co. KGaA | Alfred-Krupp-Str. 9 | 73479 Ellwangen | Germany
 P.O. Box 1363 | 73473 Ellwangen | Germany | Phone (+49) 7961 83 0 | Fax (+49) 7961 83 440

