



Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Tab**

Wire Size: **4 – 6.63 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Product Type Features

Insertion Force	Normal
-----------------	--------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Electrical Characteristics

Voltage Rating	250 V
----------------	-------

Contact Features

Quick Disconnect Terminal Type	Tab
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Unplated
Crimp Type	F-Crimp
Barrel Type	Open

Termination Features



Product Terminates To	Wire & Cable
-----------------------	--------------

Mechanical Attachment

Locking Lance Height	1.5 mm
Wire Insulation Support	With
Mating Retention Type	Locking Lance

Dimensions

Product Length	30.1 mm[1.185 in]
Compatible Insulation Diameter Range	3.4 – 5.1 mm[.134 – .2 in]
Terminal Material Thickness	.41 mm[.016 in]
Wire Size	4 – 6.63 mm²

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Packaging Features

Packaging Quantity	2500
Packaging Method	Strip/Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent



chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 180250
HHHT FSTON/FF 375 POS LOC 250 6-2 ASSY

TE Part # 2379381-1
SDE F, FASTIN-FASTON, 4.0-6.0mm2, ASSY

TE Part # 2379381-2
SDE F, FASTIN-FASTON, 4.0-6.0mm2, DIE SET

TE Part # 1-1579007-4
EXTRACTION TOOL

TE Part # 4-1579007-3
EXTRACTION TOOL KIT


Also in the Series | FASTIN-FASTON 250

Crimp Terminal Housings(195)


Insertion & Extraction Tools(2)

Quick Disconnects(216)


Customers Also Bought




TE Part #CC2649-000
[B-106-1803CS50](#)




TE Part #CC2643-000
[B-106-7502CS100](#)




TE Part #CC2637-000
[B-106-1802CS100](#)




TE Part #CC2621-000
[B-106-1501CS100](#)




TE Part #CC2631-000
[B-106-7401CS100](#)




TE Part #CC2644-000
[B-106-8502CS100](#)




TE Part #CC2628-000
[B-106-3631CS100](#)



TE Part #CC2630-000
[B-106-4631CS100](#)



TE Part #CC2641-000
[B-106-3632CS100](#)



TE Part #CC2645-000
[D-406-0003CS50](#)

Documents

Product Drawings

[FF 250 TAB 4-6MM2 BR](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_180352-1_AN.2d_dxf.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_180352-1_AN.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_180352-1_AN.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



1654742_HOUSEHOLD_APPLIANCES_RAST5

English

Product Specifications

FASTIN-FASTON CONN. .110 INCH, .187 INCH, .250 INCH, .375 INCH SRS.

English

Product Specification

English