



123456


A



B



C



D

part no. 09 32 000...		Ø	wire gauge		crimp hole depth l1	stripping length	recommended crimping tools			
silver plated			mm ²	AWG			09 99 000 0888	09 99 000 0110	09 99 000 0001	09 99 000 0377
male contact	female contact									
6109	6209	4,3	10,0	8	9,7	depending on isolation body				X
6108	6208	3,53	6,0	10	9,7	9,5				X
6107	6207	2,88	4,0	12	9,7		X	X	X	X
6106	6206	2,58	3,0	12	9,7		X	X	X	
6105	6205	2,28	2,5	14	9,7		X	X	X	
6104	6204	1,78	1,5	16	9,7		X	X	X	



All Dimensions in mm
Original Size DIN A4

Scale
2:1

Free size tol.

Ref.

Sub.



All rights reserved

Department EL PD

Created by
HELLMANN

Inspected by
RIEPE

Standardisation
SAP_WFRT

Date
16-Apr-2025

State
40 - Released

Title
Han C-SMC-male/female contacts-crimp-Ag

Doc-Key / ECM-Nr.
100821744 / UGD/009/H
500000209279

HARTING
D-32339 Espelkamp

Type
TB

Number
09320006X0X

Rev.
H

Page
1/1