

OSD2

OSD2 - OFFSET SCREWDRIVER/ DRILL ANGLE ATTACHMENT

- The OSD 2 screwdriver / drill angle attachment is the ideal solution for all screwdriving and drilling applications in restricted areas.
- 1/4" magnetic Hex bit reception accepts both standard 25 mm (C 6.3) and ball end reception (E 6.3), with bit locking mechanism.
- Metal gears and housing for smooth and precise running and excellent power transmission.
- 360° rotatable softgrip side handel for left and right hand use with 4 lock positions.
- Two step Hex shaft to fit either 1/4" (6 mm) Hex shaft or 10 mm Hex shaft.
- Industrial quality designed for use with all cordless tools in applications up to 40 Nm torque and a maximum of 1750 rpm.
- The OSD2 is capable of both drilling and screwdriving applications, offering maximum versatility.
- Only 51 mm in height for use in confined spaces.



Article Number	4932352320
Height (mm)	51
Pack quantity	1
Total length (mm)	160