



ENGLISH

## Datasheet

# RS PRO Bench floor standing pillar drill

Stock number: 181-8945

181-8946



## Bench type pillar drill

Specification :

<b>Model</b>	<b>181-8945/BS</b>
	<b>181-8946/VDE</b>
<b>Motor Power</b>	<b>350W</b>
<b>Chuck</b>	<b>13mm</b>
<b>Spindle Stroke</b>	<b>50mm</b>
<b>Spindle Taper</b>	<b>B16</b>
<b>Speed Change</b>	<b>5</b>
<b>Speed 50Hz/60 Hz</b>	<b>620-2620/740-3140 rpm</b>
<b>Swing</b>	<b>210mm</b>
<b>Table Size</b>	<b>160 x 160mm</b>
<b>Max dis. Chuck to table</b>	<b>180mm</b>
<b>Max dis. Chuck to base</b>	<b>260mm</b>
<b>Base size</b>	<b>290 x 190</b>
<b>Column</b>	<b>Φ46mm</b>
<b>Total Height</b>	<b>590mm</b>
<b>Weight</b>	<b>16/15kg</b>
<b>Packing dimension</b>	<b>450x340x250mm</b>

Features : Five speed bench drill is ideal for the hobby or DIY user

With 13mm capacity chuck compact dimension and a whole host of other useful feature

It has a depth gauge and a height adjustable tilting table with slot to clamp work piece

For safety there's a clear chuck guard and a no voltage release switch, can't start unexpectedly Should mains power fail

A front mounted reference chart has an accurate depth measurement scale which shows the 5 Available drilling speed

The chuck is mounted via a taper which allow the use of taper shank drill bits