

Eaton 250MJ25-6

Catalog Number: 250MJ25-6

Eaton Bussmann series low voltage british standard fuse, 250A, AC 415 V, V88/J, 39 x 46 mm, gU



General specifications

Product Name	Catalog Number
Eaton Bussmann series low voltage british standard fuse	250MJ25-6
	EAN
	5027590469425
Product Length/Depth	Product Height
49 mm	39 mm
Product Width	Product Weight
39 mm	150.7 g
Compliances	Certifications
CE Marked	BS
RoHS Compliant	IEC 60269
	EAC

Electrical data

Amperage Rating

250 A

Voltage rating

415 V

Voltage type

AC

Breaking capacity

80 kA

Class

Class gG/gL

Product specifications

Application

feeder pillars

Fuse type

MJ25

Fitted with:

Slotted tags

Connection

Bolt-on

Resources

Catalogs

[CA134002EN](#)

Declarations of conformity

[UKCA Feeder pillar fuse-links](#)

[CE Feeder pillar fuse-links](#)

Multimedia

[Eaton Bussmann - Red Spot fuse links](#)

Technical data sheets

[4177 MJ25 fuses](#)

Technical service bulletins

[Datasheet - 250MJ25-6](#)