

Datasheet

RS Pro Grey Self Adhesive Cable Retainer, 7 Apertures, 25 x 150mm

RS Stock No: **454-7676**



Product Details

RS Pro self adhesive cable retainer in grey colour, has 7 apertures for a perfect hold. It measures 25 x 150 mm and has rubber construction.

Features and Benefits

- Self adhesive
- 7 apertures
- Rubber construction



Specifications:

Colour	Grey
Dimensions	25 x 150 mm
Length	25 mm
Material	Rubber
Maximum Operating Temperature	+100°C
Number of Apertures	7
Operating Temperature Range	Maximum of +100°C
Self Adhesive	Yes
Width	150 mm

Application: To cover and protect all types of cables found in offices, shops, laboratories, factories exhibition halls, warehouses and anywhere where loose trailing cables are found.

Rubber: Natural rubber/SBR blend

Hardness: 75 +/- 5% hard

Halogens No halogens

Fire Retardancy: Fire retardant to BS 476 Part 7 Class 3 and European equivalent DIN Part 1 and Class B1

Conductivity: The material is non-conductive, tested to BS903 Part C5.
At 500 volts the reading was in excess of 2000 Mega ohms
At 1000 volts the reading was 205 Mega ohms

All profiles are UV stabilised for extended outdoor life.

Featuring: Snap Fit cable insertion