



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUL 2019 (201) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #1-1879457-1
TE 2500W 6R8 5% Bracket



TE Part #1-640388-0
10P MTA156 HDR ASSY RN STR F/L



TE Part #NB-PTCO-190
Pt1000, 1.2x4.0, Class C, PTFM102C1A0



TE Part #2057159-1
SFP+ 1x1 Cage Assy, Press-Fit, 20 Pin



TE Part #1676274-2
RN 0805 27K4 0.1% 10PPM 1KRL

TE Part #2-1393253-9
W68-X2Q12-10=M6/M7/M9/W6/W7

TE Part #3-647168-3
03P MTA100 HDR ASSY SM 30AU LF

TE Part #1825258-2
SPDT SL SW R/A AU

TE Part #2-1879215-4
CPF 0402 6K98 0.1% 25PPM 1K RL

TE Part #1-2176338-2
CRGCQ 0402 68R 5%

Documents

Product Drawings

MSS2250G04=DPDT SL SW VERT AU

English

CAD Files

Customer View Model

ENG_CVM_CVM_1825263-2_A.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1825263-2_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1825263-2_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.