

B1000 - K-Road S3 HRO CI SRC

Collection: Kaptiv

Upper: Water-Resistant Nubuck

Lining: SmellStop Antiodor and Antibacterial*

Midsole: Fresh'n Flex

Toecap: Aluminium

Sole: Double-Density PU/HRO Rubber i-daptive® Technology

Outer Carton: 10

Kaptiv

The first safety footwear range with stability control, designed to offer incredible dynamic comfort.

Base

Comfort is what has inspired Base Protection since its first day of activity. The company produces safety footwear, combining technology and functional requirements, to respond to professional and more demanding clients.



Standards

EN ISO 20345:2011 S3 (HRO CI SRC)

Features

- Anti-static footwear
- Water resistant upper to prevent water penetration
- 200 joules resistant toe-cap
- Puncture resistant sole
- Shock absorption in the heel region
- Heat resistant 1 minute up to 300°C
- Cold insulation up to -17°C
- Hydrocarbons resistant
- Men's width
- Orthopaedic made to measure footbed, complying with european norms DGUV112-191

B1000 - K-Road S3 HRO CI SRC**Commodity Code: 6403400000****Test House**

A.N.C.I. Servizi S.R.L (CIMAC) (Notified Body No.: NB: 0465)

Via Alberto Riva Villasanta, 3

, Italy

Cert No: F-113-00391-18 Rev 01

Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
B1000GBU36	Grey/Blue	67.0	41.0	36.0	1.2000	0.0989	8054633494578	
B1000GBU37	Grey/Blue	67.0	41.0	36.0	1.2300	0.0989	8054633494585	
B1000GBU38	Grey/Blue	67.0	41.0	36.0	1.2320	0.0989	8054633494592	
B1000GBU39	Grey/Blue	67.0	41.0	36.0	1.2500	0.0989	8054633493984	
B1000GBU40	Grey/Blue	67.0	41.0	36.0	1.3500	0.0989	8054633493991	
B1000GBU41	Grey/Blue	67.0	41.0	36.0	1.3550	0.0989	8054633494004	
B1000GBU42	Grey/Blue	67.0	41.0	36.0	1.4200	0.0989	8054633494011	
B1000GBU43	Grey/Blue	67.0	41.0	36.0	1.4700	0.0989	8054633494028	
B1000GBU44	Grey/Blue	67.0	41.0	36.0	1.5500	0.0989	8054633494035	
B1000GBU45	Grey/Blue	67.0	41.0	36.0	1.6600	0.0989	8054633494042	
B1000GBU46	Grey/Blue	67.0	41.0	36.0	1.6900	0.0989	8054633494059	
B1000GBU47	Grey/Blue	67.0	41.0	36.0	1.7000	0.0989	8054633494066	
B1000GBU48	Grey/Blue	67.0	41.0	36.0	1.7260	0.0989	8054633494073	