



fitted with

work equipment
connected load
power consumption
glare-free
system of protection
class of protection
technology
usage
luminaire body
material
color
lamp cover
weight (net)
mains lead

3 x 6W LED
color temperature 5000K
color rendering index (CRI) = 65
without
24V DC
approx. 18W
without
IP67
III
switchable
without switch

anodized aluminum
silver
4mm thick borosilicate safety glass
approx. 1.8lb (0.8kg)
built-in plug
RSFM 4/0.5M

fastening
total length
special features

fixed surface mount
20.95in (532mm)
50° beam angle



RSFM 4/0.5M

illuminance

measuring conditions: d=50cm

E_{min}: 104 lx
E_m: 869 lx
E_{max}: 2090 lx

