

LED RECHARGEABLE NECKLIGHT

Product Specifications

SPECIFICATIONS	OBS-NL1
Color	Grey/Red
Material	Aluminum/Plastic
Luminosity (Lumen)	600 (Turbo Mode - Both Lamps) 250 (High Mode - One Lamp) 30 (Low Mode - One Lamp)
Rechargeable	Yes
Battery Type	Lithium-Ion
Runtime	30s (Turbo Mode - Both Lamps) 3h (High Mode - One Lamp) 24h (Low Mode - One Lamp)
Charge Time	4h
Charging Port	USB-C
Power Bank for Charging Phones	Yes (5V, 1A)
Weight	10.2 oz / 288 g
Length	10.6 in / 270 mm
Width	9.8 in / 250 mm
Height	1.6 in / 40 mm
Storage/Operating Temperature	+15°F to +120°F / -10°C to +50°C
IP Rating	IP54
IK Rating	IK07
Dimmable	Yes
Magnet	Yes
Accessories	3-in-1 Charging Cable