

Price* : 29.84 GBP



Main

| | |
|---------------------------|-------------------|
| Range | ClimaSys |
| Product name | ClimaSys CC |
| Product or component type | Thermostat |
| Temperature setting range | 5...60 °C |
| Information displayed | Temperature in °C |


Complementary

| | |
|---------------------------------------|---|
| Input voltage | 250 V |
| Sensor type | Bimetal |
| Contacts type and composition | 1 NO/NC |
| Contact resistance | < 10 mOhm |
| Service life in cycles | >= 100000 cycles |
| Maximum switching capacity | 30 W DC 10 A 250 V AC inductive 4 A 250 V AC inductive pf: 0.6 |
| Electrical connection | 4 terminals 2.5 mm ² |
| Mounting mode | Clipped |
| Height | External : 68 mm |
| Width | External : 56 mm |
| Depth | External : 44 mm |
| Product weight | 100 g |
| Mounting location | On mounting plate 35 mm DIN rail Spacial upright Cross rails |
| Ambient air temperature for operation | -20...80 °C |
| IP degree of protection | IP20 |
| Hysteresis | 7 % |
| Number of outputs | 1 output(s) heating function 1 output(s) ventilation function |
| Material | PC |
| Colour | Light grey |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------------|---|
| Flame retardance | Self-extinguishing conforming to UL94 (material V0) |
| Product certifications | UL |

Offer Sustainability

| | |
|------------------------|---|
| RoHS (date code: YYWW) | Compliant - since 0940 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity |
|------------------------|---|

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|
